### Metal Table Screens

Now Open for Orders 3-4 Week Lead Time




Allsteel universal metal table-mounted screens offer a cleanable, easily retrofitted solution to create boundaries within the workplace. Available in 20"H and 25"H, metal screens offer users a sense of privacy while also providing a magnetic surface for posting notes or an optional marker board finish as a writable surface. Extended lateral screens offer an additional 12" boundary between users.

| Description                                 | SPLA Model       | List Price |
|---|------------------|------------|
| Mtl Table Screen, 20"H x 451/2"W (for 48"W) | ASIMTLSCRN2048   | \$780      |
| Mtl Table Screen, 20"H x 511/2"W (for 54"W) | ASIMTLSCRN2054   | \$818      |
| Mtl Table Screen, 20"H x 571/2"W (for 60"W) | ASIMTLSCRN2060   | \$859      |
| Mtl Table Screen, 20"H x 631/2"W (for 66"W) | ASIMTLSCRN2066   | \$902      |
| Mtl Table Screen, 25"H x 451/2"W (for 48"W) | ASIMTLSCRN2548   | \$896      |
| Mtl Table Screen, 25"H x 51½"W (for 54"W)   | ASIMTLSCRN2554   | \$941      |
| Mtl Table Screen, 25"H x 571/2"W (for 60"W) | ASIMTLSCRN2560   | \$988      |
| Mtl Lat Screen 20"H x 21"D (for 24"D)       | ASIMTLSCRN2024   | \$673      |
| Mtl Lat Screen 20"H x 25"D (for 27"-30"D)   | ASIMTLSCRN2030   | \$707      |
| Mtl Lat Screen 20"H x 34"D (for 36"D)       | ASIMTLSCRN2036   | \$742      |
| Mtl Lat Screen 25"H x 21"D (for 24"D)       | ASIMTLSCRN2524   | \$774      |
| Mtl Lat Screen 25"H x 25"D (for 30"D)       | ASIMTLSCRN2530   | \$813      |
| Mtl Lat Screen 25"H x 34"D (for 36"D)       | ASIMTLSCRN2536   | \$853      |
| Mtl Extended Screen 20"H x 33%"D (for 24"D) | ASIMTLEXSCRN2036 | \$757      |
| Mtl Extended Screen 20"H x 37%"D (for 30"D) | ASIMTLEXSCRN2042 | \$795      |
| Mtl Extended Screen 25"H x 33%"D (for 24"D) | ASIMTLEXSCRN2536 | \$870      |
| Mtl Extended Screen 25"H x 37"D (for 30"D)  | ASIMTLEXSCRN2542 | \$914      |

Offered in 32 standard Allsteel powder-coat paint finishes, including a marker board finish. P2 is \$20 upcharge, P3 is \$40 upcharge, P6 (marker board) is a \$100 upcharge. Bracket will match the finish of the screen.

- Screens are offered as extended lateral (for 24" or 30"D worksurfaces), lateral (for 24", 30", or 36"D surfaces), or table-mounted configurations (for 48" through 66"W worksurfaces).
- Screen depths are undersized to accommodate
   Further™ or Altitude® worksurface depths but can
   also be added to panel systems or tables products.
- Brackets attach to the top of the worksurface using an industrial grade adhesive. Installation does not require any drilling or defacing of the worksurface.
   Screens and brackets may be removed in the future, if desired
- The front of the bracket has a beveled zinc cap, and the back of the bracket has exposed hardware.
   Brackets are non-handed so that the front and back can be oriented either direction, based on the application.
- Screens meet or exceed ANSI/BIFMA X5.5-2014 Sections 4.6 and 9.









### Acrylic Table Screens

Now Open for Orders 3-4 Week Lead Time



Allsteel universal acrylic table mounted screens offer a cleanable, easily retrofitted solution to create boundaries within the workplace. Available in 20"H and 25"H, acrylic screens offer users protection and personal division within a workspace. Extended lateral screens offer an additional 12" boundary between users.

| Description                                  | SPLA Model        | List Price |
|--|-------------------|------------|
| Acry Table Screen, 20H" x 451½"W (for 48"W)  | ASIACRYSCRN2048   | \$780      |
| Acry Table Screen, 20"H x 51½"W (for 54"W)   | ASIACRYSCRN2054   | \$818      |
| Acry Table Screen, 20"H x 571/2"W (for 60"W) | ASIACRYSCRN2060   | \$859      |
| Acry Table Screen, 20"H x 631/2"W (for 66"W) | ASIACRYSCRN2066   | \$902      |
| Acry Table Screen, 25"H x 451½"W (for 48W")  | ASIACRYSCRN2548   | \$896      |
| Acry Table Screen, 25"H x 511½"W (for 54"W)  | ASIACRYSCRN2554   | \$941      |
| Acry Table Screen, 25"H x 57½"W (for 60"W)   | ASIACRYSCRN2560   | \$988      |
| Acry Table Screen, 25"H x 631/2"W (for 66"W) | ASIACRYSCRN2566   | \$1,037    |
| Acry Lat Screen 20"H x 21"D (for 24"D)       | ASIACRYSCRN2024   | \$673      |
| Acry Lat Screen 20"H x 25"D (for 30"D)       | ASIACRYSCRN2030   | \$707      |
| Acry Lat Screen 20"H x 34"D (for 36"D)       | ASIACRYSCRN2036   | \$742      |
| Acry Lat Screen 25"H x 21"D (for 24"D)       | ASIACRYSCRN2524   | \$774      |
| Acry Lat Screen 25"H x 25"D (for 30"D)       | ASIACRYSCRN2530   | \$813      |
| Acry Lat Screen 25"H x 34"D (for 36"D)       | ASIACRYSCRN2536   | \$853      |
| Acry Extended Screen 20"H x 33%"D (for 24"D) | ASIACRYEXSCRN2036 | \$757      |
| Acry Extended Screen 20"H x 33%"D (for 24"D) | ASIACRYEXSCRN2042 | \$795      |
| Acry Extended Screen 20"H x 37"D (for 30"D)  | ASIACRYEXSCRN2536 | \$870      |
| Acry Extended Screen 25"H x 37"D (for 30"D)  | ASIACRYEXSCRN2542 | \$914      |

- Screens are offered as extended lateral (for 24" or 30"D worksurfaces), lateral (for 24", 30", or 36"D surfaces), or table-mounted configurations (for 48" through 66"W worksurfaces).
- Screen depths are undersized to accommodate
   Further™ or Altitude® worksurface depths but can
   also be added to panel systems or tables products.
- Brackets attach to the top of the worksurface using an industrial grade adhesive. Installation does not require any drilling or defacing of the worksurface.
   Screens and brackets may be removed in the future, if desired.
- The front of the bracket has a beveled zinc cap, and the back of the bracket has exposed hardware.
   Brackets are non-handed so that the front and back can be oriented either direction, based on the application.
- Screens are made of 0.170" thick high-impact clear acrylic.
- Screens meet or exceed ANSI/BIFMA X5.5-2014 Sections 4.6 and 9.

Bracket color must be specified. Available in Allsteel Standard Paints. P2 is \$10 upcharge, P3 is \$15 upcharge.





### Acrylic Freestanding Screens

Now Open for Orders 3-4 Week Lead Time

Acrylic Freestanding Screens offer a cleanable, transparent solution to create a protective barrier between users. Models with a transaction cut-out are a solution for reception and other front-desk applications. Varying screen sizes provide solutions for different types of spaces. From a large reception desk to a smaller check-in space, this screen solution blocks germs without interrupting communication.

- Screens are supported by two black feet. Feet are only available in a black finish.
- Feet dimensions are 12"H x 10 1/8"W.
- Screens are offered as a freestanding solution and do not adhere or mount to a worksurface or tabletop.
- Transaction cut-out screens stand 36"H and are offered in 30", 36", and 48"W.
- Freestanding screen without a cut-out is available in 24" or 30"H and 30", 36", or 48"W.
- Screens are made of 0.220" thick high-impact clear acrylic.

| Description                                 | SPLA Model         | List Price |
|---|--------------------|------------|
| Acry Freestanding Screen Cutout 36"H x 30"W | ASIACRYFSSCRNC3630 | \$368      |
| Acry Freestanding Screen Cutout 36"H x 36"W | ASIACRYFSSCRNC3636 | \$376      |
| Acry Freestanding Screen Cutout 36"H x 48"W | ASIACRYFSSCRNC3648 | \$384      |
| Acry Freestanding Screen 24"H x 30"W        | ASIACRYFSSCRNX2430 | \$329      |
| Acry Freestanding Screen 24"H x 36"W        | ASIACRYFSSCRNX2436 | \$335      |
| Acry Freestanding Screen 24"H x 48"W        | ASIACRYFSSCRNX2448 | \$350      |
| Acry Freestanding Screen 36"H x 30"W        | ASIACRYFSSCRNX3630 | \$368      |
| Acry Freestanding Screen 36"H x 36"W        | ASIACRYFSSCRNX3630 | \$376      |
| Acry Freestanding Screen 36"H x 48"W        | ASIACRYFSSCRNX3648 | \$384      |










Allsteel foot and arm pulls allow for hands-free entry on any latch-less door. A hands-free operation helps to prevent cross-contamination in high traffic areas. The hands-free pulls are shipped with mounting hardware to accommodate either metal or solid wood doors and are offered in either a pack of 5 or 15.

- Hands-free pulls are ideal for high-traffic areas.
- Hands-free pulls can be installed in minutes using the included mounting hardware.
- Toothed edge on foot pull ensures a no-slip grip.
- Offered in Textured Titanium (P8V) and Textured Black (P6P).



**Arm Pull** 7 %" H x 2 ½"W x 4 ½"D




Foot Pull

1%" H x 5"W x 3 1/4"D

| Description                               | SPLA Model    | List Price |
|---|---------------|------------|
| Allsteel Door Foot Pull 5 PACK            | ASIFOOTPULL5  | \$255      |
| Allsteel Door Foot Pull 15 PACK           | ASIFOOTPULL15 | \$720      |
| Allsteel Hands Free Door Arm Pull 5 PACK  | ASIARMPULL5   | \$255      |
| Allsteel Hands Free Door Arm Pull 15 PACK | ASIARMPULL15  | \$720      |







The Allsteel height-adjustable table foot control allows for hands-free adjustment at any Altitude® A6 or A3 table. Hands-free operation helps prevent the spread of germs, making this control a great solution for individual or shared workspaces.

- Compatible with the existing Altitude A3 and the new Altitude A6 height-adjustable tables.
- · Available in grey only.
- Wireless design offers clean and functional solution.
- Can be paired with a standard control pad for dual control function.
- Easy to install instructions for retrofitting current workstations or adding on to new Altitude A6 workstations.
- Requires 2 AAA batteries. Batteries not included.





1%" x 7%"W x 41%"D

| Description                     | SPLA Model | List Price |
|---------------------------------|------------|------------|
| A3/A6 Wireless Foot Control Pad | A6FOOTCNTL | \$240      |






## Hand Sanitizer Solutions

Now Open for Orders 3-4 Week Lead Time



Allsteel offers an easy and accessible sanitizing solution, helping employees stay bacteria-free while moving throughout the office. Incorporating freestanding stations within the facility aids in preventing the transfer of germs between meetings and high-traffic areas. Bottle holders at individual workstations free up valuable workspace to allow for easy surface cleaning while promoting more frequent sanitizing.

- Ideal for high-traffic areas and workstations.
- Available freestanding on base and mounted to panel wall or tool rail and tile.
- Metal freestanding base for added stability. Drip tray prevents sanitizer spills.
- Holder is compatible with most standard hand sanitizer dispensers.
- Easy installation: holder for panel or tool rail and tile can be attached through the pre-drilled holes or via double-sided tape. Additional mounting holes can be drilled to fit a non-standard dispenser.
- Velcro attachment can be used to hold other disinfectants.
- · Hand sanitizer dispenser sold separately.



| Description   | SPLA Model                      | List Price |
|---|---------------------------------|------------|
| Freestanding Hand Sanitizer Stand<br>with Drip Tray           | ASISANSTND                      | \$315      |
| Panel Mount / Wall Mount Hand<br>Sanitizer Bottle Holder      | SPLA-HC-ACCYHRDWP:M505015.PAINT | \$94       |
| Tool Tile / Tool Rail Mounted Hand<br>Sanitizer Bottle Holder | SPLA-HC-ACCYHRDWP.M505017.PAINT | \$94       |

Offered in 32 standard Allsteel powdercoat paint finishes. P2 is \$13 upcharge; P3 is \$22 upcharge.








Having a place to hold hand sanitizers either on panels or architectural walls, keeps items in consistent locations and prevents cluttering a table or worksurface. The hand sanitizer holder can be inserted into Beyond's slotted standards between panels. The holder is designed to fit most 8 oz bottles of hand sanitizer.

This model contains the following parts: a left-hand and a right-hand bracket that fit into Beyond's 5%" slotted standards, a metal holder that screws into the bracket, and a hardware pack with 4 screws. Only one bracket is needed for installation and the holder can be positioned in a right, left or centered location.

- The metal mount can be finished in any Beyond or Aspect standard painted metal finishes. It will be painted in an anodized-like silver powder coat if anodized clear is selected.
- To attach the mount to Aspect, no bracket is needed. Simply screw the bracket into Aspect between the door jamb and panel vertical.
- If mounting into a panel system, a different bracket is needed to work with furniture's ½" slotted standards (see Hand Sanitizer Solutions).
- The mount can also be screwed into drywall with no bracket needed.







Metal Holder

Beyond Bracket

| Description                       |        | SPLA Model                    | List Price |
|-----------------------------------|--------|-------------------------------|------------|
| Hand Sanitizer Holder – Clear Ano | dized* | SPLW-SANITIZER.M505403.AALCLR | \$75       |
| Hand Sanitizer Holder – Painte    | d S    | PLW-SANITIZER.M505403.PNT**   | \$75       |

<sup>\*</sup>Note: Holder will be painted in a light silver powder coat to match anodized.





<sup>\*\*</sup>Choose from 30 Beyond and Aspect standard painted metal options. See Beyond and Aspect specification guides for full listing of finishes.

<sup>4-5</sup> week lead time when ordered with Aspect finishes. 6-8 week lead time when ordered with Beyond finishes.

### Altitude® A8 Screens Now Available in **Contourett**

A Durable & Easy-to-Clean Polyurethane Now Open for Orders





Altitude A8 screens create a natural privacy barrier above and below the worksurface. The A8 screen extends 21¾" above and 10" below the worksurface, creating a boundary around your personal workspace in a clean and attractive way. As workspace design evolves, creating a sense of physical privacy and personal space can help promote individual well-being. Adding a privacy screen, like an A8 screen, to compatible work surfaces offers the much-needed personal perimeter we now look for in our workspace.

A8 screen kits (U, Rectangle) are now available in Contourett, a non-tackable 100% polyurethane, a durable and easy-to-clean surface that allows for the use of a variety of cleaning agents.

Material Cleaning Resources →

#### Statement of Line







48" 54" 60" 66" 72" U Screen Kit

#### Available to order as a Standard Special in Contourett colors



| Size / Shape  | SPLA Model                               |
|---------------|--|
| 48" U         | SPLA-A8-FABSCRNPNTA.M505257.FABRIC.PAINT |
| 54" U         | SPLA-A8-FABSCRNPNTA.M505258.FABRIC.PAINT |
| 60" U         | SPLA-A8-FABSCRNPNTB.M505259.FABRIC.PAINT |
| 66" U         | SPLA-A8-FABSCRNPNTB.M505260.FABRIC.PAINT |
| 72" U         | SPLA-A8-FABSCRNPNTB.M505261.FABRIC.PAINT |
| 48" Rectangle | SPLA-A8-FABSCRNPNTA.M505262.FABRIC.PAINT |
| 54" Rectangle | SPLA-A8-FABSCRNPNTA.M505263.FABRIC.PAINT |
| 60" Rectangle | SPLA-A8-FABSCRNPNTB.M505264.FABRIC.PAINT |
| 66" Rectangle | SPLA-A8-FABSCRNPNTB.M505265.FABRIC.PAINT |
| 72" Rectangle | SPLA-A8-FABSCRNPNTB.M505266.FABRIC.PAINT |


# Specifying for Freestanding Worksurfaces


Altitude A8 screens are designed to fit on Altitude worksurfaces, which are undersized by 2" to allow for height-adjustable motion. This is a common design for height-adjustable worksurfaces, but there are a few steps to take to verify non-Altitude worksurfaces are compatible.

- 1. Understand measurements of worksurface
- 2. Match with correct A8 screen size
- Consider clearance of modesty screen and mounting brackets

Example: 48" Altitude Worksurface (AF5RS4824) is actually 46". A 48" U-Screen kit would be the correct screen size to specify with this worksurface.

Allsteel Customer Support is available to verify when needed.







### How to Clean

#### Contourett

- · For wet spills, gently blot with dry cloth to remove spill.
- · For dried spills, gently work the spill in a non-aggressive circular motion using a damp cloth, making sure to not oversaturate the fabric.
- For dried stains, use a mixture of Tide or Oxiclean and warm water (1 teaspoon of soap for every 16 ounces of water). Follow instructions for dried spills above. Make sure to wipe away any excess soap left behind and remove any moisture with a dry cloth.
- For non-liquid spills, always remove excess contaminant from surface before cleaning. The use of a soft brush or soft abrasive can be used to remove dried contaminants before performing liquid cleaning.
- For healthcare related stains, a water-to-bleach solution of 5:1 is recommended. Rinse cleaned area with water.
- For stains requiring the use of a solvent, spray the solvent directly onto the stain and allow it to sit for 2-3 minutes, avoiding over saturating the fabric. Follow directions for dried stains above.
- Always allow fabric to air dry.

#### **Approved Cleaners for Contourett**

It is important to remember that after use of any cleaning agent, the fabric should be rinsed with water and wiped dry to remove any remaining residue or moisture. Approved cleaning agents include Shockwave, Recon, Benefect, Microban, Greased Lightning Degreaser, Lysol Wipes, Diluted bleach solution (5:1 water to bleach), Dispatch Disinfectant Towels with bleach, PDI Sani-Hands Wipes, PDI Super Sani-Cloth Germicidal Disposable Wipes, Diversity Morning Mist Neutral Disinfectant Cleaner, Virex 256, Fantastik, Oxycide, Formula 409.



